F-CLAMP-C-3B



KwikClamp™ Hanger for power & fiber cables, 22-34 mm, triple stack; includes hardware

Product Classification

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note CommScope® standard product in Europe, the Middle East, and

Africa

General Specifications

Cables per Hanger

Color Black

Hanger Type KwikClamp[™] hanger

Mounting 3–25 mm angle iron | 3–25 mm flat plate | Round Member 8-

25 mm

Dimensions

Maximum Stack Height 3

 Height
 269 mm | 10.591 in

 Width
 45 mm | 1.772 in

 Length
 44 mm | 1.732 in

Compatible Cable Diameter Range 22–34 mm

Compatible Diameter, maximum34 mm1 .339 inCompatible Diameter, minimum22 mm0 .866 inHanger Spacing, maximum1.83 m6 .004 ft

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Page 1 of 2



F-CLAMP-C-3B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Corrosion Resistance, minimum with no degredation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 21

Weight, gross 5.367 kg | 11.832 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power