

LS2-HMDM-20M-D



D-CLASS LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 7/16 DIN Male, 20m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX® SureFlex®
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	20 m 65.617 ft
Nominal Size	3/8 in

Logo Image

LS2-HMDM-20M-D



Electrical Specifications

3rd Order IMD Dynamic	-116 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.106	26
1700–2200 MHz	1.106	26
2200–2700 MHz	1.106	26
3400–3800 MHz	1.222	20
4000–6000 MHz	1.288	18

Jumper Assembly Sample Label

LS2-HMDM-20M-D



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition