

# C400-HMHM-1M

---

CNT-400 CNT® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 1m



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-400

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CNT-400
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	1 m   3.281 ft
<b>Nominal Size</b>	0.400 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.101	26.4

## Jumper Assembly Sample Label

# C400-HMHM-1M

---



## Included Products

- 400PHM-C-CR    –    Type 4.3-10 Male connector for CNT-400 braided cable
- CNT-400    –    CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket