

FD3-AC144J00JBDP1BB-US



Standard FDH3000, 132F loaded bottom pole mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Dielectric Loose Tube Cable, 200ft stub, using 1x144F cable containing both 1x132 distribution and a 1x12F feeder, Build America Buy America (BABA) Compliant

- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

| | |
|------------------------------|---|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |
| Government Funding | Build America Buy America (BABA) coming soon* |

General Specifications

| | |
|--|-----------------------------|
| Access | Front |
| Cable Type | Dry Dielectric - Loose Tube |
| Color | Putty white |
| Distribution Cables, quantity | 1 |
| Distribution Ports, quantity | 144 |
| Fibers per Distribution Cable, quantity | 132 |
| Fibers per Feeder Cable, quantity | 12 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pole |
| Splitter Slots, quantity | 18 |

Dimensions

| | |
|---------------|------------------|
| Height | 914.4 mm 36 in |
| Width | 533.4 mm 21 in |
| Depth | 355.6 mm 14 in |

FD3-AC144J00JB DP1BB-US

Cable Length 60.96 m | 200 ft

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground | Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet