

243095-37



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Block style hangers (4 stack), includes M10 bolts and hardware, 305 mm (11.87 in) length

Product Classification

Product Type	Hardware kit
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Thread Size	M10
--------------------	-----

Dimensions

Maximum Stack Height	4
Length	301.498 mm 11.87 in
Nominal Size	1-1/4 in 1-5/8 in

Material Specifications

Material Type	Stainless steel 304
----------------------	---------------------

Packaging and Weights

Height, packed	254 mm 10 in
Width, packed	88.9 mm 3.5 in
Length, packed	330.2 mm 13 in
Included	Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts
Packaging quantity	10
Weight, gross	1.361 kg 3 lb

* Footnotes

Maximum Stack Height	Fiber, Hybrid, Power
-----------------------------	----------------------