

C400F-HMNR



CNT-400-FR CNT® Jumper with interface types 4..3-10 Male and N Male Right Angle. Fire Retardancy Test Method IEC 60332

Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-400

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	CNT-400
Interface, Connector A	4.3-10 Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	0.400 in
---------------------	----------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
10–1000 MHz	1.101	26.36

Jumper Assembly Sample Label

C400F-HMNR

Batch Manufacturing Date (two digit year and week)
Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE Andrew Solutions™
F4-DMDM-2M-D — Part Number
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES 12US220001242 — Serial Number

