

TW-4310-SP



Slim profile coupling torque wrench for 4.3-10 connectors, 22 mm opening, 8Nm torque

Product Classification

Product Type	Wrench
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Application	Torques 4.3-10 connectors
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	22.25 mm 0.876 in
-----------------------	---------------------

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	±0.8 N-m (±7.1 in lb)
Torque Value	70.806 in lb 8 N-m

Packaging and Weights

Height, packed	165.001 mm 6.496 in
Width, packed	145.009 mm 5.709 in
Length, packed	330.022 mm 12.993 in
Packaging quantity	1
Weight, gross	0.89 kg 1.962 lb