

4




3

2

1

- 1.0 GENERAL NOTES  
 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]  
 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (XX)  
 1.3 3D DIGITAL FILES ARE FOR REFERENCE. IN CASE OF CONFLICT FOLLOW PDF DRAWING
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS  
 3.1 BREAK SHARP EDGES AND DEBURR PART FOR SAFE HANDLING  
 3.2 GALVANIZE PER ASTM A123  
 3.3 MARK WITH PART NUMBER, REVISION, AND VENDOR ID WITH ETCH, STAMP OR LABEL. CHARACTERS TO BE 0.12" TO 0.24" HIGH AND LEGIBLE TO THE UNAIDED EYE.
- 4.0 TEST
- 5.0 PACKAGING  
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	YMENG 05AUG24	BA1025 40201651CMO
B	UPDATED NOTES AND REMOVED BARE LEVEL	YMENG 14AUG24	BA1025 40202145CMO



**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER	
1 PLACE .X[X] ± 0.2[6.3]	3 PLACE .XXX[X] ± 0.060[1.5]	<b>P-100-HD</b>	
2 PLACE .XX[X] ± 0.12[3.0]	ANGLES ± 2°		
FINISH GALV A123		MATERIAL A500	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.3M-1994	NAME	DATE	<b>PANEL ANT STANDOFF BRK 12" 2-7/8" PIPE</b>
	CE YMENG	05AUG24	
	RW YMENG	08/13/2024	
	AD BA1025	08/15/2024	
	RE YMENG	08/15/2024	
ECN 40202145CMO			SCALE <b>1:16</b>
			DOCUMENT NO. <b>P-100-HD</b>
SIZE	Auth Group	INSL	MODEL
C			VERSION
			STATUS
		REVISION	DRAWING
		01	VERSION
		RE	STATUS
		A	REVISION
		01	RE
		B	SHEET
			1 OF 1

DENSITY		lbs/in³
MASS	56.17	lbs
VOLUME	198.49	in³
SURFACE AREA	3246.35	in²
HEIGHT	120.0"	
LENGTH	12.5"	
WIDTH	2.88"	