

FD3-AB096J00MMOV1



Enhanced Mini FDH, 96F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, feed/F1 input is capable of receiving 12F via a loose tube pigtailed splice tray, and using (8) 12F MPO connectors for distribution/patch

- 12-fiber MPO connector based modular design enables simple connections

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Color	Putty white
Distribution Cables, quantity	8
Distribution Ports, quantity	96
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole Wall
Splice Tray Chip Type	Mechanical
Splice Tray Included, quantity	1
Splice Tray Type Included	12-fiber, single element
Splicing Capacity, maximum	12
Splitter Slots, quantity	8

Dimensions

Height	584.2 mm 23 in
Width	330.2 mm 13 in
Depth	203.2 mm 8 in

FD3-AB096J00MMOV1

Cable Length 0 m | 0 ft

Enclosure Size Mini

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground | Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet