

FD3-MN360J00M0ME0B



Indoor FDH 3000 w/ 432f Shell, 360f distribution loaded, no splitters included, MPO distribution connectors, and a 24f Feeder using Spliced Stranded Loose Tube Pigtailes

Indoor FDH 3000 w/ 432f Shell, 360f distribution loaded, no splitters included, MPO distribution connectors, and a 24f Feeder using Spliced Stranded Loose Tube Pigtailes

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Functionality	Patching Splicing
Adapters, quantity	360
Color	Putty white
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	360

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

