

# 760258800

---



GigaREACH Modular Plug Kit, 8 pin configuration, Cat 6, UTP, 100PC

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Modular plug

## General Specifications

### ANSI/TIA Category

6

### Cable Type

U/UTP (unshielded)

### Color

Clear

### Conductor Type

Solid | Stranded

### Interface

RJ45

### Positions/Loaded Contacts

8

### Termination Type

IDC

## Dimensions

### Compatible Cable Diameter, maximum

7.87 mm | 0.31 in

### Compatible Cable Diameter, minimum

6.35 mm | 0.25 in

### Compatible Insulated Conductor Diameter, maximum

1.07 mm | 0.042 in

### Compatible Insulated Conductor Diameter, minimum

0.99 mm | 0.039 in

### Contact Plating Thickness

1.27 µm

### Compatible Conductor Gauge, solid

21 AWG

## Material Specifications

### Contact Base Material

Copper alloy

### Contact Plating Material

Gold over nickel | Phosphor Bronze

### Material Type

Polycarbonate

## Mechanical Specifications

# 760258800

---

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Safety Standard** UL 1863

## Packaging and Weights

**Packaging quantity** 100

**Packaging Type** Bag