# 760258356 | PPL-FA-4U-HCM



Propel 4RU front access fiber panel for Propel XFrame. Accepts 24, 16 fiber or 48, 8 fiber Propel ULL modules, splice cassettes or 8 port/4 port adapter packs

- Panel comes with 24 carriers to allow for all front access using standard Propel components. Incoming cable and patch cords are routed at the front of the panel
- HCM (Horizontal Cable Management) panels: HCM panels maximize density within the frame. Patch cords are routed across the front of the panel providing maximum frame density
- For use with 8 fiber or 16 fiber Propel components

#### Product Classification

Portfolio CommScope®

**Product Type** Fiber patch panel

Product Brand Propel

Product Series PPL

## General Specifications

**Color** Gray

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 4

Shelf Movement Fixed

#### Dimensions

 Height
 178 mm | 7.008 in

 Width
 483 mm | 19.016 in

### Material Specifications

Material Type Aluminum | Steel

### **Environmental Specifications**

Safety Standard UL



# 760258356 | PPL-FA-4U-HCM

## Packaging and Weights

Packaging quantity

**Weight, net** 4.128 kg | 9.1 lb