

# A-VF1-SXX2G

## Base Product



## PSC Cabinet Samsung Fitout 2

PSC cabinet with internal racking to accommodate upto 3 servers and transmission. The following features are included in the cabinet:

- 3U Eltek PSU
- 4 No. 4kW Rectifiers
- 2 No. 100Ah Battery
- 12-way DCDU for Samsung Radios
- 3-way SPD Protected DCDU for Pole Mounted 4G Radios.

## Product Classification

**Regional Availability** EMEA

**Product Type** Outdoor cabinet

## General Specifications

**Access** Front and rear door

**Accessories** Cable plate | External alarm connection | Hangers | In-ground root | Plinth

**Cabinet Type** Baseband cabinet | Power cabinet | Transmission cabinet

**Cable Entry Location** Bottom

**Color** Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

**Cooling** 175 mm fan (1)

**Door Security** Internal door contact for front door | Swing handle with European profile cylinder for front door

**Door Type, front** Key lock (included) | Non-removable

**Door, quantity** 2

**Front Door Type** Single hinged

**Lock Type** Internal latch for rear door | Key lock for front door

**Mounting** In-ground root | Plinth

**Radios Included** None

## Dimensions

**Height** 1,721.866 mm | 67.79 in

**Width** 822.96 mm | 32.4 in

# A-VF1-SXX2G

---

**Depth** 599.948 mm | 23.62 in

## Material Specifications

**Finish** Powder coated

**Material Type** Galvanized steel

## Environmental Specifications

**Qualification Standards** IEC 60529, IP54

## Packaging and Weights

**Weight, net** 399.996 kg | 881.84 lb