

# FMX-ATT-BARVM00-24

---



FMT Fiber Optic MicroVAM Panel, 24 module capacity, 2RU, 19 in, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber VAM panel
<b>Product Series</b>	FMT

## General Specifications

<b>Functionality</b>	Multiplexing   Splitting
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Putty white
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	24
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	381 mm   15 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

# FMX-ATT-BARVM00-24

---

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

