

LSX-771082-A-SPL

LSX Fiber Termination/Splice Panel 4 Ru, 96 - SC/UPC, Singlemode Stranded

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	LSX

General Specifications

Functionality	Patching Splicing
Application	Used in LSX-style frames only
Cable Stub Type	Pigtails, stranded
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Fixed
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	96

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	381 mm 15 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

LSX-771082-A-SPL

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

