

FMS Fiber Optic Termination Panel, 1U, 19 in, 6 LC/UPC, singlemode, black

Product Classification

Regional Availability	India
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FMS

General Specifications

Functionality	Patching
Body Style	Symmetrical
Color	Black
Interface, front	LC/UPC
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Trays Included, quantity	1
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	6

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	320 mm 12.598 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature -25 °C to +75 °C (-13 °F to +167 °F)
Storage Temperature -30 °C to +80 °C (-22 °F to +176 °F)

Packaging and Weights

Included Mounting hardware
Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

