

760236398 | OCFPS1U-P123200L2



OCFPS Fiber Optic Splitter Panel, one 2x32, symmetrical, planar, singlemode, LC/APC, 1U, 19 in, gray

OBSOLETE

This product was discontinued on: September 18, 2023

Replaced By:

1RU-SP1232001 1RU panel, 2X32 split ratio, 1 splitter, LC/APC connectors
1RU SPLTR PNL 2X32 APC/LC

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	OCFPS

General Specifications

Device Type	Patch panel
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Circuits, quantity	1
Distribution Type	2 x 32 splitter
Interface, front	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	43.5 mm 1.713 in
Width	440 mm 17.323 in
Depth	210 mm 8.268 in

Ordering Tree

760236398 | OCFPS1U-P123200L2

OCFPS 1U - X X X X X X

Shelf Type

1HU	1 RU High 19" wide
-----	--------------------

Splitter Grade

A	FBT type
P	Planar grade P
O	Planar grade O (low loss)

Number of Splitters

	Shelf type 1	
	Grade A	Grade P/O
1 x 2	16	-
2 x 2	16	-
1 x 4	-	6
2 x 4	-	6
1 x 8	-	6
2 x 8	-	6
1 x 16	-	2
2 x 16	-	2
1 x 32	-	2
2 x 32	-	1
1 x 64	-	1
2 x 64	-	1

Connector Type

S1	SC/UPC
S2	SC/APC 8°
S3	SC/APC 9°
L1	LC/UPC
L2	LC/APC

Split Ratio

00	Symmetrical
----	-------------

Number of Output Ports

02	... x 2 splitter
04	... x 4 splitter
08	... x 8 splitter
16	... x 16 splitter
32	... x 32 splitter
64	... x 64 splitter

Number of Input Ports

1	1 x ...splitter
2	2 x ...splitter

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant

Compliant

