

760082586 | RK4P45-36S



Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	4 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	45
Rail Mounting Hole	3/8 in

Dimensions

Height	2,133.6 mm 84 in
Channel Width	76.2 mm 3 in
Width	518.16 mm 20.4 in
Depth	1,219.2 mm 48 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Mechanical Specifications

760082586 | RK4P45-36S

Static Load Rating 907.2 kg | 2,000.031 lb

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Base pan | Forty #12-24 x 1/2 in mounting screws | Forty M6 cage nuts | Four vertical rack rails | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

Packaging quantity 1

Packaging Type Flat packed

Weight, net 49.9 kg | 110.011 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

