

FDP-D4PS72048



CMT Fiber Termination/Splice Panel, 48 SC/UPC, pre-terminated with pigtailed, singlemode, 5RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	CMT

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Interface, front	SC/UPC
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	5
Total Ports, quantity	48

Dimensions

Height	222.25 mm 8.75 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

FDP-D4PS72048

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

