

FDP-E2KS22036



CMT Fiber Termination/Splice Panel, 36 FC/UPC, pre-terminated with pigtails, singlemode, 7RU, 19 in, putty white

OBSOLETE

This product was discontinued on: March 1, 2018

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	CMT

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Interface, front	FC/UPC
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	7
Total Ports, quantity	36

Dimensions

Height	304.8 mm 12 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Material Specifications

FDP-E2KS22036

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

