

# CPC6642-02 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

---

PowerSUM D8PS Stranded Cordage Modular Patch Cord, Light Blue Jacket



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Brand</b>	PowerSUM
<b>Product Series</b>	CPC

## General Specifications

<b>ANSI/TIA Category</b>	5e
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Stranded
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	RJ45 plug
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	Light blue
<b>Pairs, quantity</b>	4
<b>Wiring</b>	T568B

## Dimensions

<b>Cable Assembly Length, minimum (ft)</b>	1
<b>Cable Assembly Length, maximum (ft)</b>	100
<b>Cable Assembly Length, minimum (m)</b>	1
<b>Cable Assembly Length, maximum (m)</b>	30

# CPC6642-02 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Electrical Specifications

<b>dc Resistance, maximum</b>	0.3 ohm
<b>Safety Voltage Rating</b>	300 V

## Ordering Tree

CPC     -

9    10    11    12

### Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

### Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

### UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

### Length

12	XXX
----	-----

### Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Material Specifications

<b>Contact Plating Material</b>	Precious metals
---------------------------------	-----------------

# CPC6642-02 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

---

**Material Type** Copper alloy | Polycarbonate

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times  
**Plug Retention Force, minimum** 133 N | 29.9 lbf

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Environmental Space** Non-plenum  
**Flammability Rating** UL 94 V-0  
**Safety Standard** Anatel | ETL | cETL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

848482253 1074D LB 4/24 RVAR	-	PowerSUM 1074D Category 5e U/UTP Cable, non-plenum, light blue jacket, 4 pair count, variable length, reel
---------------------------------	---	--