

Fiber Optic Intra Facility Cable, Multimode, LC/UPC to LC/UPC, 22 ft

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber distribution cable assembly
<b>Product Series</b>	IFC

## General Specifications

<b>Color, boot A</b>	Beige
<b>Color, boot B</b>	Beige
<b>Color, connector A</b>	Beige
<b>Color, connector B</b>	Beige
<b>Connector A, quantity</b>	12
<b>Connector B, quantity</b>	12
<b>Interface, Connector A</b>	LC/UPC
<b>Interface, Connector B</b>	LC/UPC
<b>Jacket Color</b>	Orange
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Cord Length</b>	6.71 m   22.014 ft
--------------------	--------------------

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM1

## Environmental Specifications

<b>Environmental Space</b>	Riser
----------------------------	-------

## Packaging and Weights

**Packaging quantity** 1

Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

