

T-10-NM



Termination Load, 0–3000 MHz

OBSOLETE

This product was discontinued on: December 31, 2019

Replaced By:

T-10-UW-NM

Termination Load, 0–6000 MHz, Not for PIM-rated applications

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Termination Load

General Specifications

Device Type Termination Load

Application Indoor/Outdoor

Color Black

Inner Contact Plating Silver

Interface N Male

Outer Contact Plating Trimetal

Dimensions

Length 53.5 mm | 2.106 in

Diameter, maximum 35 mm | 1.378 in

Electrical Specifications

Return Loss, minimum 23 dB

Average Power, maximum 10 W

Impedance 50 ohm

Operating Frequency Band 0 – 3000 MHz

VSWR 1.15

T-10-NM

Environmental Specifications

Operating Temperature	-35 °C to +50 °C (-31 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	68 mm 2.677 in
Width, packed	53 mm 2.087 in
Length, packed	58 mm 2.283 in
Volume	209 mm ³ 0.013 in ³
Weight, gross	0.14 kg 0.309 lb
Weight, net	0.11 kg 0.243 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

