

F4P43-HM-5M

FSJ4-50B SureFlex® Jumper with interface types 4.3-10 Male and open end, 5m



Product Classification

Product Type	Coaxial wireless cable
Product Series	FSJ4-50B

General Specifications

Body Style, Connector A	Straight
Interface, Connector A	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	1/2 in

Electrical Specifications

DTF, Connector A	-34 dB
-------------------------	--------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
710–806 MHz	1.201	20.8
806–960 MHz	1.151	23.1
1420–1530 MHz	1.151	23.1
1700–2180 MHz	1.151	23.1
2535–2655 MHz	1.201	20.8

Jumper Assembly Sample Label

F4P43-HM-5M



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition