




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 11469PC: RELEASE TO PRODUCTION PER EAO 609604.	16JUN21 YD	LZL / TJL



FFHHTTVV-65A-R8

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER																					
0 PLACE X ±	2 PLACE .XX ±																						
1 PLACE .X ±	ANGLES ±																						
FINISH		MATERIAL																					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)		<table border="1"> <thead> <tr> <th>NAME</th> <th>DATE</th> <th>TITLE</th> </tr> </thead> <tbody> <tr> <td>CE YD1013</td> <td>16JUN21</td> <td rowspan="5">PRODUCT DRAWING</td> </tr> <tr> <td>RW YD1013</td> <td>06/22/2021</td> </tr> <tr> <td>AD ZL1025</td> <td>06/22/2021</td> </tr> <tr> <td>RE QS1002</td> <td>06/22/2021</td> </tr> <tr> <td>ECN 11469PC</td> <td></td> </tr> </tbody> </table>		NAME	DATE	TITLE	CE YD1013	16JUN21	PRODUCT DRAWING	RW YD1013	06/22/2021	AD ZL1025	06/22/2021	RE QS1002	06/22/2021	ECN 11469PC							
NAME	DATE	TITLE																					
CE YD1013	16JUN21	PRODUCT DRAWING																					
RW YD1013	06/22/2021																						
AD ZL1025	06/22/2021																						
RE QS1002	06/22/2021																						
ECN 11469PC																							
SCALE 1:4		DOCUMENT NO. FFHHTTVV-65A-R8-L																					
SIZE A2		<table border="1"> <thead> <tr> <th colspan="3">MODEL</th> <th colspan="3">DRAWING</th> <th rowspan="2">SHEET</th> </tr> <tr> <th>VERSION</th> <th>STATUS</th> <th>REVISION</th> <th>VERSION</th> <th>STATUS</th> <th>REVISION</th> </tr> </thead> <tbody> <tr> <td>00</td> <td>RE</td> <td>A</td> <td>00</td> <td>RE</td> <td>A</td> <td>1 OF 1</td> </tr> </tbody> </table>		MODEL			DRAWING			SHEET	VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	00	RE	A	00	RE	A	1 OF 1
MODEL			DRAWING			SHEET																	
VERSION	STATUS	REVISION	VERSION	STATUS	REVISION																		
00	RE	A	00	RE	A	1 OF 1																	

DENSITY	g/mm ³
MASS	grams
VOLUME	mm ³
SURFACE AREA	mm ²
HEIGHT	
LENGTH	
WIDTH	