

F1RNA-PNMNR-32



FSJ1RK-50B SureFlex® Jumper with interface types N Male and N Male
Right Angle, 32 ft

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1RK-50B

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	9.75 m 31.988 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-75 dBm
DTF, Connector A	-28 dB
DTF, Connector B	-25 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
1850–1910 MHz	1.22	20.08

Jumper Assembly Sample Label

FIRNA-PNMNR-32



Environmental Specifications

EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	a1
Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition