

7845390-1003 | CAP L2 35LT/35HT F-DC



Carrier Access Point with MIMO 2x2 Radio Modules for Low Power TDD 3500 Applications, Fiber Fed, External DC powered

OBSOLETE

Replaced By:

7845390-1036 Carrier Access Point with MIMO 2x2 Radio Modules for Low Power TDD 3500 Applications, Fiber Fed, External DC powered
CAP L2 35LT/35HT F-DC

Product Classification

Product Type	Access point
Product Brand	ERA®
Product Series	CAP L2

General Specifications

Fan Kit	Not included
Fed Type	Fiber fed
Note	CEPT Case B compliance – B42+ max. ant Gain 5 dBi CEPT Case B compliance – B43+ max. ant Gain 10 dBi Detailed Product Specifications are available. Please contact your local CommScope representative. OFCOM compliance – B42+, B43+ max. ant. Gain 9 dBi, 10 dBi respectively
Power Class	Low
Powering Type	External DC powered

Electrical Specifications

License Band	TDD 3500
Voltage Range	-57 to -42 Vdc

Included Products

7846281-01 – Wall Mounting bracket to mount a CAP L2 to a wall
Wall Mounting bracket CAP L2

7846281-01 | Wall Mounting bracket CAP L2



Wall Mounting bracket to mount a CAP L2 to a wall

Product Classification

Product Type Mounting kit

Product Brand ERA®

Dimensions

Height 220 mm | 8.661 in

Width 351 mm | 13.819 in

Depth 116 mm | 4.567 in

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

