

7845389-1032 | UAP2 7E/17E/19/37T F-DC



Carrier Access Point with MIMO 2x2 Radio Module for Low Power USA 700, USA 750, LMR 750, AWS 1700, PCS 1900, and C-Band TDD Applications, Fiber fed, DC

Product Classification

| | |
|-----------------------|--------------|
| Product Type | Access point |
| Product Brand | ERA® |
| Product Series | UAP2 |

General Specifications

| | |
|----------------------|----------------------------------------------------------------------------------------------------|
| Antenna Type | MIMO Antenna |
| Fan Kit | Included |
| Fed Type | Fiber fed |
| Note | Detailed Product Specifications are available. Please contact your local CommScope representative. |
| Power Class | Low |
| Powering Type | External DC powered |

Electrical Specifications

| | |
|----------------------|------------------------------------------------------------|
| License Band | AWS 1700 C-Band LMR 750 PCS 1900 USA 700 USA 750 |
| Voltage Range | -57 to -42 Vdc |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

