

# MC-PK-238-238

---



Monopole Platform Pipe Mount Kit, with (1) 2-3/8 to 2-3/8 in Crossover plates and (1) 2-3/8 to 3-1/2 in clamp plus (1) 2-3/8" OD x 96" Pipe

## Product Classification

**Product Type** Pipe mount kit

## General Specifications

**Mounting** Round member

**Pipe, quantity** 1

## Dimensions

**Pipe Length** 2,438.4 mm | 96 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 60.325 mm | 2.375 in

**Pipe Outer Diameter** 60.325 mm | 2.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Crossover plates | Plain end pipes | U-bolts

**Packaging quantity** 1

**Weight, net** 32.84 kg | 72.4 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

