

SA-4C



PIM-Guard® Four-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8" holes for angle adapter integration. It includes four 3/4" holes for Snap-in hangers, supporting three 4-30mm or two 36-42mm cable stacks per hole

Product Classification

| | |
|----------------------|--------------------------------------|
| Product Type | Adapter |
| Product Brand | PIM-Guard® |
| Ordering Note | CommScope® standard product (Global) |

General Specifications

| | |
|---------------------|--|
| Adapter Type | Stand-off adapter |
| Color | Black |
| Mounting | 3/4 in through hole 3/8 in through hole Round member |

Dimensions

| | |
|-----------------------------|---------------------|
| Maximum Stack Height | 3 |
| Height | 54.61 mm 2.15 in |
| Outside Width | 40.132 mm 1.58 in |
| Outside Length | 86.36 mm 3.4 in |

Material Specifications

| | |
|----------------------|--------------------|
| Material Type | Engineered plastic |
|----------------------|--------------------|

Mechanical Specifications

| | |
|---------------------------|--|
| Maximum Loading | Double stack for hangers SSH-2630, SSH-3642 Triple stack for hangers SSH-411, SSH-1117 |
| Vibration Survival | ≥4 hours at resonant frequency |

Environmental Specifications

| | |
|---|--------------------------------------|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
| Environmental Strength Capability | Double cable weight |
| UV Resistance, minimum with no degradation | ≥1000 hours |

SA-4C

Packaging and Weights

| | |
|---------------------------|--------------------|
| Height, packed | 17 cm 6.693 in |
| Width, packed | 13 cm 5.118 in |
| Length, packed | 10 cm 3.937 in |
| Packaging quantity | 10 |
| Weight, gross | 0.27 kg 0.595 lb |

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power