

SF-PK-278-278



Sector Frame Pipe Mount Kit, with (2) 2-7/8 to 2-7/8 in Crossover plates and (1) 2-7/8" OD x 96" Pipe

Product Classification

Product Type Pipe mount kit

General Specifications

Mounting Round member

Pipe, quantity 1

Dimensions

Pipe Length 2,438.4 mm | 96 in

Mounting Diameter, maximum 73.025 mm | 2.875 in

Mounting Diameter, minimum 73.025 mm | 2.875 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Crossover plates | Plain end pipes | U-bolts

Packaging quantity 1

Weight, net 45.5 kg | 100.31 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

