

RG142-NMNM-M5

RG142 Braided Jumper with interface types N Male and N Male, 0.5m



Product Classification

Product Type	Braided cable assembly
Product Series	RG142

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	RG142
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	0.5 m 1.64 ft
---------------	-----------------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.152	23

Jumper Assembly Sample Label

RG142-NMNM-M5



Included Products

- RG142 - RG142 50 Ohm Braided Coaxial Cable
- RG142TNM-CR - Type N Male for RG142 braided cable