

SF-PK-238-278



Sector Frame Pipe Mount Kit, with (2) 2-7/8 to 2-3/8 in Crossover plates and (1) 2-3/8" OD x 120" Pipe

Product Classification

Product Type Pipe mount kit

General Specifications

Mounting Round member

Pipe, quantity 1

Dimensions

Pipe Length 3,048 mm | 120 in

Mounting Diameter, maximum 73.025 mm | 2.875 in

Mounting Diameter, minimum 60.325 mm | 2.375 in

Pipe Outer Diameter 60.325 mm | 2.375 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Crossover plates | Plain end pipes | U-bolts

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

