

760257045 | PPL-CM-8AU-16AP-2X1-SM-BEU



Propel ULL Singlemode Conversion Module, (2) MPO-08/APC non-pinned ports rear, (1) MPO-16/APC pinned port front

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- This component requires 2 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber module
Product Brand	Propel
Product Series	PPL

General Specifications

Functionality	Breakout
Color, front	Gray
Color, rear	Gray
Data Module Type	Fiber Conversion Module
Interface, front	MPO
Interface Feature, front	Internal shutters MPO Pinned
Interface, rear	MPO
Interface Feature, rear	Internal shutters MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	16
Total Ports, quantity, front	1
Total Ports, quantity, rear	2

Dimensions

Height	11 mm 0.433 in
Width	65 mm 2.559 in
Depth	170 mm 6.693 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.7 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL 62368

Packaging and Weights

Packaging quantity	1
---------------------------	---