

FD3-MN432J00MOMKOC



Indoor FDH 3000 w/ 432f Shell, 432f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Ivory Colored Plenum Loose Tube Cable with stubbed MT ends

Indoor FDH 3000 w/ 432f Shell, 432f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Ivory Colored Plenum Loose Tube Cable with stubbed MT ends

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Functionality	Patching Splicing
Adapters, quantity	432
Color	Putty white
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	432

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

FD3-MN432J00MOMKOC
