

Fiber Optic Cable, 8-fiber, OM3, ULSZH, 1000 m, aqua

**OBSOLETE**

This product was discontinued on: June 13, 2018

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Fibers per Subunit, quantity</b>	8
<b>Jacket Color</b>	Aqua
<b>Total Fiber Count</b>	8

## Dimensions

<b>Cable Length</b>	1000 m   3,280.84 ft
<b>Diameter Over Jacket</b>	6 mm   0.236 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	90 mm   3.543 in
<b>Minimum Bend Radius, unloaded</b>	60 mm   2.362 in
<b>Tensile Load, long term, maximum</b>	600 N   134.885 lbf
<b>Tensile Load, short term, maximum</b>	1000 N   224.809 lbf

## Optical Specifications

<b>Fiber Type</b>	OM3
-------------------	-----

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	1.50 dB/km @ 1,300 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492AAAC (OM3)

## Environmental Specifications

<b>Installation temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Dca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s2
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d1
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)

## Packaging and Weights

<b>Cable weight</b>	35 kg/km   23.519 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable