CW8112-000 | BUDI-2S-T-08L1ES



BUDI™ Fiber Optic Wall mount Enclosure, 8 LC/UPC ports, single element FIST splice trays for SMOUV splices

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeFiber wall box

Product Brand BUDI™
Product Series BUDI-2S

General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceLC/UPCMountingWallPort, quantity8

Splice Tray Construction SE (Single element)

Splicing Capacity, maximum 8

Dimensions

 Height
 260 mm | 10.236 in

 Height, with cover
 285 mm | 11.22 in


 Width
 155 mm | 6.102 in

 Depth
 60 mm | 2.362 in


Dimension Drawing



CW8112-000 | BUDI-2S-T-08L1ES







Material Specifications

Enclosure Material TypeLSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor/Outdoor

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



COMMSCOPE®

CW8112-000 | BUDI-2S-T-08L1ES

