CW8864-000 | BUDI-2S-T-02S1ES



BUDI™ Fiber Optic Wall mount Enclosure, 2 SC/UPC adapters, single element FIST splice trays for SMOUV splices

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

Product Classification

Regional Availability EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber wall box

Product Brand BUDI™
Product Series BUDI-2S

General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceSC/UPCMountingWallPort, quantity2

Splice Tray Construction SE (Single element)

Splicing Capacity, maximum 2

Dimensions

 Height
 260 mm | 10.236 in

 Height, with cover
 285 mm | 11.22 in


 Width
 155 mm | 6.102 in

 Depth
 60 mm | 2.362 in


Dimension Drawing



CW8864-000 | BUDI-2S-T-02S1ES







Material Specifications

Enclosure Material TypeLSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor/Outdoor

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



COMMSC PE°

CW8864-000 | BUDI-2S-T-02S1ES

