FD3-MM144J00V00E0C



IFDH 3000 Indoor Fiber Distribution Hub, 144F, SC/APC, loose tube /stranded pigtails, spliced input/dist., 48FF

Product Classification

Enclosure Size

Regional Availability	North America Fiber distribution hub
Product Type Product Series	IFDH 3000
General Specifications	
Functionality	Patching Splicing
Access	Front
Adapters, quantity	144
Cable Type	Pigtails - Stranded
Color	Putty white
Distribution Cables, quantity	12
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	48
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	144
Splitter Slots, quantity	18
Dimensions	
Height	736.6 mm 29 in
Width	533.4 mm 21 in
Depth	368.3 mm 14.5 in
Cable Length	30.48 m 100 ft

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2024

Medium



FD3-MM144J00V00E0C

Material Specifications

Finish	Powder coated
Material Type	Aluminum
Optical Specifications	
Fiber Mode	Singlemode

Environmental Specifications

Environmental Space

Indoor

1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2024

