

# 760237333 | HD-iP-4U-384F-LC-DM-TS-FX

HD iPATCH 4U 384F-LC Distribution Module, TeraSPEED, Fixed Shelf



## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber patch panel   |
| <b>Product Brand</b>         | iPatch®   imVision®   |
| <b>Product Series</b>        | HD   IPATCH   |

## General Specifications

|                              |                             |
|------------------------------|-----------------------------|
| <b>Color</b>                 | Black + Silver gray (front) |
| <b>Intelligence Type</b>     | iPatch® enabled             |
| <b>Interface, front</b>      | LC/UPC                      |
| <b>Rack Units</b>            | 4                           |
| <b>Shelf Movement</b>        | Fixed                       |
| <b>Total Ports, quantity</b> | 192                         |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 177.8 mm   7 in      |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 553.97 mm   21.81 in |

## Material Specifications

|                      |       |
|----------------------|-------|
| <b>Material Type</b> | Steel |
|----------------------|-------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

RCM

Compliant to electrical safety & telecommunications requirements

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

