

# TFP-5TT00-000B

---



TFP Fiber Termination/Splice Panel, unloaded, termination only rack /cabinet mount panel, 5 RU, 19 in, black, T-handle latch close

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	TFP

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Patch Cord Entry Location</b>	Front, left side   Front, right side
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	5
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	222.25 mm   8.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	399.29 mm   15.72 in

## Ordering Tree

# TFP-5TT00-000B

TFP - X X AP X X X X X X

## Number of Fiber Ports

12	12 fiber ports: 6 LC adapters; 6 SC duplex adapters; 12 ST adapters
24	24 fiber ports: 12 LC adapters

## Pack Orientation

L	angle left
R	angle right

## Adapter Style

Multimode Connectors	
C3	SC duplex (beige)
C4	SC duplex (aqua)
Q1	LC (beige)
Q2	LC (aqua)
T1	ST®
Singlemode Connectors	
C8	SC UPC duplex (blue)
A2	SC APC duplex (green)
Q5	LC UPC (blue)
T2	ST UPC

## Pigtail Length

Leave	Adapters only
Blank	
3	3 meter pigtails

## Pigtail Type

Leave	Adapters only
Blank	
B	Singlemode stranded
E	Multimode stranded

## Fiber Size

Leave	Adapters only
Blank	
B	OM1 - 62.5/125 Multimode
D	OM3 - 50/125 LOMMF 300m
S	Singlemode

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1
<b>Weight, net</b>	7.194 kg   15.86 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

# TFP-5TT00-000B

---

ROHS

Compliant

UK-ROHS

Compliant

