760200352 | 360CM12-4x6-LS



G2 4x6 Multimode OM4 Conversion Module, 6 MPO male ports

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber module

General Specifications

Functionality Breakout

Adapters, quantity, front 6
Adapters, quantity, rear 4

Color, frontAquaColor, housingBlackColor, rearGray

Data Module TypeStandardInterface, frontMPO

Interface Feature, front Standard

Interface, rear MPO

Interface Feature, rear Male | Reduced footprint

Polarity Method B

Shuttered No
Total Fibers, quantity 48
Total Ports, quantity, front 6

Dimensions

 Height
 27.94 mm | 1.1 in

 Width
 91.44 mm | 3.6 in

 Depth
 109.22 mm | 4.3 in

Optical Specifications

COMMSC PE°

760200352 | 360CM12-4x6-LS

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED® 550

Insertion Loss Change, mating0.3 dBInsertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.5 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingMaximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

