760201194 | 360-iP-MFTP-E-1U-BLANK



SYSTIMAX 360™ iPatch® FTP Evolve Modular Panel, 24 port without jacks

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

1

Portfolio SYSTIMAX®

Product Type RJ45 patch panel

Product Brand SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category 6A

Cable TypeShieldedColorSilver

Intelligence Type iPatch® enabled

Panel Style Straight

Rack Units

Total Ports, quantity 24

Wiring T568A | T568B

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 206.5 mm | 8.13 in

 Compatible Diameter Over Dielectric, maximum
 1.168 mm | 0.046 in

Electrical Specifications

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface 1,500 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

COMMSCOPE®

760201194 | 360-iP-MFTP-E-1U-BLANK

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

