

# 760202556 | 360-iP-1100A-E-GS6-1U-24



SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Angled Patch Panel, 24 port

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

SYSTIMAX®

### Product Type

RJ45 patch panel

### Product Brand

SYSTIMAX 360™ | iPatch®

## General Specifications

### ANSI/TIA Category

6A

### Cable Type

Unshielded

### Color

Cool gray

### Intelligence Type

iPatch® enabled

### Panel Style

Angled

### Rack Units

1

### Total Ports, quantity

24

### Wiring

T568A | T568B

## Dimensions

### Height

44.45 mm | 1.75 in

### Width

482.6 mm | 19 in

### Depth

266.7 mm | 10.5 in

### Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

### Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

## Electrical Specifications

### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

### Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

# 760202556 | 360-iP-1100A-E-GS6-1U-24

**Insulation Resistance, minimum** 500 MOhm

## Material Specifications

**Contact Plating Material** Precious metals

**Material Type** Acrylonitrile butadiene styrene (ABS) | Polycarbonate

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

**Plug Insertion Life, test plug** IEC 60603-7 compliant plug

**Plug Retention Force, minimum** 133 N | 29.9 lbf

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** ACMA | CE | ETL | UL

## Packaging and Weights

**Included** Cable management bar | Four "A" labels | Four #12-24 mounting screws | Instruction sheet | Panel | Twenty-four cable ties

**Packaging quantity** 1

**Weight, net** 0.816 kg | 1.8 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

