760239081 | UDS-6U-WH-LC-B-ULL



UDS 6RU splice panel, 432 duplex LC/UPC ports, Enhanced Method B, White, ULL

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series UDS

General Specifications

Application Preloaded with 36 UDS modules

Color White

Interface, front LC/UPC

Pigtail Assembly Type 12-fiber, ribbon

Pigtails Included, quantity 36

Rack Units 6

Shelf Movement Sliding

Splice Trays Included, quantity 12

Total Ports, quantity 432

Dimensions

 Height
 266.7 mm | 10.5 in

 Width
 444.5 mm | 17.5 in

 Depth
 609.6 mm | 24 in

Optical Specifications

Insertion Loss, maximum 0.25 dB

Environmental Specifications

Safety Standard CUL US 1863

COMMSCOPE®

760239081 | UDS-6U-WH-LC-B-ULL

Packaging and Weights

Weight, net 20.412 kg | 45 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

