#### 760240028 FACT-3ERHPL2S



FACT® Fiber Optic Patch/Splice Chassis, gray, 3E high, 144-port, singlemode, loaded with LC/APC adapters and C-grade pigtails, SMOUV splice tray type, right-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

#### Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio** CommScope®

**Product Type** Fiber patch/splice chassis

**Product Brand FACT® Product Series FACT** 

## General Specifications

**Functionality** Patching | Splicing

**Application** Compatible with FIST-GR3-style frames

**Body Style** Right-hand patch

Color Gray

**Growth Configuration** Fully loaded LC/APC Interface, front Right sided

**Pigtail Assembly Type** 12-fiber, stranded

Pigtails Included, quantity 144

**Patch Cord Routing** 

Rack Type EIA 19 in

**Rack Units** 2.1

**Shelf Movement** Slidina

Splicing Capacity, maximum 144

**COMMSCOPE®** 

# 760240028 | FACT-3ERHPL2S

**Splicing Type** SMOUV

Total Ports, quantity 144

**Transmission Standards** ETSI EN 300 019-1-3 | IEC 61300-3-30


### **Dimensions**

 Height
 92.85 mm | 3.656 in

 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

### Ordering Tree



## **Optical Specifications**

Fiber Mode Singlemode

**Fiber Type** G.657.A1

Performance Grade Standard C grade

Insertion Loss, maximum0.5 dBReturn Loss, minimum50 dB



# 760240028 | FACT-3ERHPL2S

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-20 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \left(-4 \, ^{\circ}\text{F to } +176 \, ^{\circ}\text{F}\right)$ 

Flammability Rating UL 94 V-0

## Packaging and Weights

**Included** Mounting hardware for FACT frame

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### \* Footnotes

**Performance Grade** Guarantee to meet IEC 61755-1 Random Mating requirement

