760240067 | FACT-2ELHPS2S-0100F



FACT® Fiber Optic Pre-cabled Chassis, gray, 2E high, 48-port, singlemode, loaded with SC/APC adapters and C-grade pigtails, SMOUV splice tray type, 10m indoor/outdoor microsheath cable, left-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber patch chassis, with indoor/outdoor cable

Product Brand FACT®
Product Series FACT

General Specifications

Functionality Patching

Application Compatible with FIST-GR3-style frames

Body Style Left-hand patch

Cable Stub Type Indoor/outdoor, microcable

Color Gray

Growth Configuration Fully loaded

 Interface, front
 SC/APC

 Interface, rear
 Stub tail

Patch Cord Routing Left sided

Rack Type EIA 19 in

Rack Units 1.4

Shelf Movement Sliding



760240067 | FACT-2ELHPS2S-0100F

Splicing Capacity, maximum 48

Splicing Type SMOUV

Total Ports, quantity 48

Transmission Standards ETSI EN 300 019-1-3 | IEC 61300-3-30

Dimensions


 Height
 61.9 mm | 2.437 in

 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

 Cable Length
 10 m | 32.808 ft

Ordering Tree



COMMSC PE°

760240067 | FACT-2ELHPS2S-0100F

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A1

Performance Grade Standard C grade

Insertion Loss, maximum0.5 dBReturn Loss, minimum50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire Performance Dca

Flammability Rating UL 94 V-0

Packaging and Weights

Included Mounting hardware for FACT frame

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

