


# FD3-AJ864J2TLFBP4

---



## FDH 3000 Fiber Distribution Large Cabinet

### Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000

### General Specifications

<b>Access</b>	Front and rear door
<b>Cable Type</b>	Armored - Ribbon
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	2
<b>Distribution Ports, quantity</b>	864
<b>Fibers per Distribution Cable, quantity</b>	432
<b>Fibers per Feeder Cable, quantity</b>	48
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pad
<b>Split Ratio</b>	Symmetrical
<b>Splitter Slots, quantity</b>	48
<b>Splitter Type</b>	1 x 32
<b>Splitter, quantity</b>	2

### Dimensions

<b>Height</b>	1,238.25 mm   48.75 in
<b>Width</b>	1,220.47 mm   48.05 in
<b>Depth</b>	497.33 mm   19.58 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Large

# FD3-AJ864J2TLFBP4

---

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Environmental Specifications

<b>Environmental Space</b>	Above ground
----------------------------	--------------

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

