

# FD3-AR072J00M00P8



Mini FDH 3000 Fiber Distribution Hub, 72-fiber shell, 72 fibers loaded, SC /APC, distribution patch, feeder pigtails

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000
<b>Warranty</b>	One year

## General Specifications

<b>Access</b>	Front
<b>Color</b>	Putty white
<b>Distribution Ports, quantity</b>	72
<b>Fibers per Feeder Cable, quantity</b>	8
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pole   Wall
<b>Splitter Slots, quantity</b>	4

## Dimensions

<b>Height</b>	482.6 mm   19 in
<b>Width</b>	330.2 mm   13 in
<b>Depth</b>	203.2 mm   8 in
<b>Enclosure Size</b>	Mini

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Environmental Specifications

# FD3-AR072J00M00P8

---

<b>Environmental Space</b>	Aerial
<b>Qualification Standards</b>	Telcordia GR-3123-CORE   Telcordia GR-3125-CORE

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--