

# FD3-PA096J1AM4320

---



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, 32-splitter module, ribbon pigtails, 96 splice cap., 12F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Hub in a pedestal
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Pigtails - Ribbon
<b>Color</b>	Putty white
<b>Distribution Ports, quantity</b>	96
<b>Fibers per Feeder Cable, quantity</b>	12
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pedestal
<b>Splice Tray Included, quantity</b>	4
<b>Splice Tray Type Included</b>	24-way, heat shrink
<b>Splicing Capacity, maximum</b>	96
<b>Split Ratio</b>	Symmetrical
<b>Splitter Slots, quantity</b>	6
<b>Splitter Type</b>	1 x 32
<b>Splitter, quantity</b>	1

## Dimensions

<b>Enclosure Size</b>	Small
-----------------------	-------

# FD3-PA096J1AM4320

---

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Molded plastic

## Environmental Specifications

<b>Environmental Space</b>	Above ground
----------------------------	--------------

## Packaging and Weights

<b>Included</b>	Cable clamps (3)
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

